

# PLANTRONICS

VPAT 13, Product: UC USB Hearing Aid Compatible (HAC) Headsets, USB Amplifier Combinations:

Over the Head USB Noise cancelling Stereo: C420, C420-M, C610, C610-M, C620, C620-M, C720, C720-M, C520, C520-M, C3220, C3225

Over the Head USB Noise cancelling Mono: C3210, C3215

Over the Head USB Noise cancelling Stereo: Operated with DA45M Stereo QD W/ D261N

Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA45M Mono QD W/ HW251N /HW261N

Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA45M Mono QD W/ HW291N /HW301N /HW710 /HW720

Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA80/DA90 QD W/ HW510D /HW520D /HW710D /HW720D

Over the Head USB Noise cancelling Convertible: Operated with DA90 QD W / HW530D, HW540D

Over the Head USB Noise cancelling Stereo: Operated with DA60 In-line Stereo QD W/ D261N

Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA60 In-line Mono QD W/ HW251N /HW261N

Over the Head USB Noise cancelling Mono/Binaural: HW251N-USB, HW715USB/HW725USB

Over the Head USB Noise cancelling Stereo: D261N-USB

Over the Ear/Over the head convertible USB Noise cancelling Mono: HW535USB (Over the Ear), HW545USB (OTE, Over the Head)

**Summary Table  
Voluntary Product Accessibility Template**

<i>Criteria</i>	<b>Supporting Features</b>	<b>Remarks and explanations</b>
Section 1194.21 Software Applications and Operating Systems	<b>Not Applicable</b>	Not a software or Operating System product.
Section 1194.22 Web-based internet information and applications	<b>Not Applicable</b>	Not a web-based application.
Section 1194.23 Telecommunications Products	<b>Supports</b>	VPAT 13 covers UC/Call Center Hearing Aid Compatible (HAC) Headsets operated with the following amplifiers/ Interfaces: DA45, DA40, DA60, DA90; with QD and In-line controlled USB pod products.
Section 1194.24 Video and Multi-media Products	<b>Not Applicable</b>	Not a video or multimedia product.
Section 1194.25 Self-Contained, Closed Products	<b>Not Applicable-</b>	Not a self-contained or closed product.
Section 1194.26 Desktop and Portable Computers	<b>Not Applicable</b>	Not a desktop or portable computer.
Section 1194.31 Functional Performance Criteria	<b>Supports</b>	All VPAT 13 Listed Products support all Functional Performance Criteria.

**VPAT 13, Product: UC USB Hearing Aid Compatible (HAC) Headsets, USB Amplifier Combinations:**

**Over the Head USB Noise cancelling Stereo: C420, C420-M, C610, C610-M, C620, C620-M, C720, C720-M, C520, C520-M, C3220, C3225**

**Over the Head USB Noise cancelling Mono: C3210, C3215**

**Over the Head USB Noise cancelling Stereo: Operated with DA45M Stereo QD W/ D261N**

**Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA45M Mono QD W/ HW251N /HW261N**

**Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA45M Mono QD W/ HW291N /HW301N /HW810 /HW720**

**Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA90 QD W/ HW510D /HW520D /HW710D /HW720D**

**Over the Head USB Noise cancelling Convertible: Operated with DA90 QD W / HW530D, HW540D**

**Over the Head USB Noise cancelling Stereo: Operated with DA60 In-line Stereo QD W/ D261N**

**Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA60 In-line Mono QD W/ HW251N/HW261N**

**Over the Head USB Noise cancelling Mono/Binaural: HW251N-USB, HW715USB/HW725USB**

**Over the Head USB Noise cancelling Stereo: D261N-USB**

**Over the Ear/Over the head convertible USB Noise cancelling Mono: HW535USB (Over the Ear), HW545USB (OTE, Over the Head)**

**Section 1194.23 Telecommunications Products - Detail  
Voluntary Product Accessibility Template**

<i>Criteria</i>	<b>Supporting Features</b>	<b>Remarks and explanations</b>
(a) Telecommunications products or systems which provide a function allowing voice communication and which do not themselves provide a TTY functionality shall provide a standard non-acoustic connection point for TTYs. Microphones shall be capable of being turned on and off to allow the user to intermix speech with TTY use.	<b>Not Applicable</b>	USB headsets do not have an interface to VCO and HCO TTY's.
(b) Telecommunications products which include voice communication functionality shall support all commonly used cross-manufacturer non-proprietary standard TTY signal protocols.	<b>Not Applicable</b>	USB headsets do not have an interface to VCO and HCO TTY's.
(c) Voice mail, auto-attendant, and interactive voice response telecommunications systems shall be usable by TTY users with their TTYs.	<b>Not Applicable</b>	USB headsets do not have an interface to VCO and HCO TTY's.
(d) Voice mail, messaging, auto-attendant, and interactive voice response telecommunications systems that require a response from a user within a time interval, shall give an alert when the time interval is about to run out, and shall provide sufficient time for the user to indicate more time is required.	<b>Not Applicable:</b>	This requirement applies to voice mail, messaging, auto-attendant and IVR systems. It does not apply to headsets.
(e) Where provided, caller identification and similar telecommunications functions shall also be available for users of TTYs, and for users who cannot see displays.	<b>Not Applicable:</b>	This requirement applies to caller identification and similar functions. It does not apply to headsets.

<p>(f) For transmitted voice signals, telecommunications products shall provide a gain adjustable up to a minimum of 20 dB. For incremental volume control, at least one intermediate step of 12 dB of gain shall be provided.</p>	<p><b>Supports</b></p>	<p>Fine and / or coarse volume controls in each Pod and headset assembly, or Volume Control Software; allows the product to meet this clause.</p>
<p>(g) If the telecommunications product allows a user to adjust the receive volume, a function shall be provided to automatically reset the volume to the default level after every use.</p>	<p><b>Supports through Equivalent Facilitation</b></p>	<p>The origin of this rule was to protect multiple users of public payphones who have different needs for increased volume. Headsets tend to be worn by a single user. The Plantronics USB headsets allow users to adjust volume. Although volume controls for the amplifiers do not reset automatically, circuitry or software in each headset assembly will protect users from loud sounds regardless of volume setting.</p>
<p>(h) Where a telecommunications product delivers output by an audio transducer which is normally held up to the ear, a means for effective magnetic wireless coupling to hearing technologies shall be provided.</p>	<p><b>Supports</b></p>	<p>The listed headsets meet the FCC Hearing Aid Compatibility Act (HAC) requirements of 47 CFR 68.317 &amp; the Telecommunications Telephone Terminal Equipment Magnetic Field and Acoustic Gain Requirements of ANSI/TIA/EIA 504A Feb 1998 and ANSI/TIA 920A.</p>
<p>(i) Interference to hearing technologies (including hearing aids, cochlear implants, and assistive listening devices) shall be reduced to the lowest possible level that allows a user of hearing technologies to utilize the telecommunications product.</p>	<p><b>Supports</b></p>	<p>USB Headsets and amplifiers do not possess circuitry capable of generating interference per ANSI/IEEE C63.19 Standard.</p>
<p>(j) Products that transmit or conduct information or communication, shall pass through cross-manufacturer, non-proprietary, industry-standard codes, translation protocols, formats or other information necessary to provide the information or communication in a usable format. Technologies which use encoding, signal compression, format transformation, or similar techniques shall not remove information needed for access or shall restore it upon delivery.</p>	<p><b>Supports</b></p>	<p>Headsets do not interfere with communications and do not remove information.</p>
<p>(k)(1) Products which have mechanically operated controls or keys shall comply with the following: Controls and Keys shall be tactilely discernible without activating the controls or keys.</p>	<p><b>Supports</b></p>	<p>All VPAT 13 Products Listed Comply with this provision: All Controls and Keys are tactilely discernible without activating them.</p>
<p>(k)(2) Products which have mechanically operated controls or keys shall comply with the following: Controls and Keys shall be operable with one hand and shall not require tight grasping, pinching, twisting of the wrist. The force required to activate controls and keys shall be 5 lbs. (22.2N) maximum.</p>	<p><b>Supports</b></p>	<p>All VPAT 13 Products Listed Comply with this provision:</p>
<p>(k)(3) Products which have mechanically operated controls or keys shall comply with the following: If key repeat is supported, the delay before repeat shall be adjustable to at least 2 seconds. Key repeat rate shall be adjustable to 2 seconds per character.</p>	<p><b>Not Applicable</b></p>	<p>This requirement applies to alphanumeric keyboard entry. VPAT13 products do not have alphanumeric keyboards.</p>

(k)(4) Products which have mechanically operated controls or keys shall comply with the following: The status of all locking or toggle controls or keys shall be visually discernible, and discernible either through touch or sound.	<b>Supports</b>	All USB In-line amplifier controls have visual and tactile status indicators.
---	-----------------	---

**Section 1194.31 Functional Performance Criteria - Detail  
Voluntary Product Accessibility Template**

<b>Criteria</b>	<b>Supporting Features</b>	<b>Remarks and explanations</b>
(a) At least one mode of operation and information retrieval that does not require user vision shall be provided, or support for Assistive Technology used by people who are blind or visually impaired shall be provided.	<b>Supports</b>	Support for people who are blind or visually impaired is provided through headset amplifier controls that are tactilely or audibly discernible.
(b) At least one mode of operation and information retrieval that does not require visual acuity greater than 20/70 shall be provided in audio and enlarged print output working together or independently, or support for Assistive Technology used by people who are visually impaired shall be provided.	<b>Supports</b>	Support for people who are visually impaired is provided through headset amplifier controls that are tactilely or audibly discernible.
(c) At least one mode of operation and information retrieval that does not require user hearing shall be provided, or support for Assistive Technology used by people who are deaf or hard of hearing shall be provided.	<b>Supports with Exception</b>	Support for people who are deaf or hard of hearing is provided through the listed headsets that are Hearing Aid Compatible(HAC). There is no VCO or HCO TTY interface capability on a USB wired Headset.
(d) Where audio information is important for the use of a product, at least one mode of operation and information retrieval shall be provided in an enhanced auditory fashion, or support for assistive hearing devices shall be provided.	<b>Supports</b>	VPAT 13 Listed Headsets comply with the FCC Hearing Aid Compatibility Act (HAC).
(e) At least one mode of operation and information retrieval that does not require user speech shall be provided, or support for Assistive Technology used by people with disabilities shall be provided.	<b>Not Applicable</b>	USB headsets do not have an interface to VCO and HCO TTY's.
(f) At least one mode of operation and information retrieval that does not require fine motor control or simultaneous actions and that is operable with limited reach and strength shall be provided.	<b>Supports</b>	USB Headsets & USB In-line Pod Amplifiers support this rule.

**VPAT 13, Product: UC USB Hearing Aid Compatible (HAC) Headsets, USB Amplifier Combinations:**

**Over the Head USB Noise cancelling Stereo: C420, C420-M, C610, C610-M, C620, C620-M, C720, C720-M, C520, C520-M, C3220, C3225**

**Over the Head USB Noise cancelling Mono: C3210, C3215**

**Over the Head USB Noise cancelling Stereo: Operated with DA45M Stereo QD W/ D261N**

**Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA45M Mono QD W/ HW251N /HW261N**

**Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA45M Mono QD W/ HW291N /HW301N /HW710 /HW720**

**Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA90 QD W/ HW510D /HW520D /HW710D /HW720D**

**Over the Head USB Noise cancelling Convertible: Operated with DA90 QD W / HW530D, HW540D**

**Over the Head USB Noise cancelling Stereo: Operated with DA60 In-line Stereo QD W/ D261N**

**Over the Head USB Noise cancelling Mono/ Binaural: Operated with DA60 In-line Mono QD W/ HW251N/HW261N**

**Over the Head USB Noise cancelling Mono/Binaural: HW251N-USB, HW715USB/HW725USB**

**Over the Head USB Noise cancelling Stereo: D261N-USB**

**Over the Ear/Over the head convertible USB Noise cancelling Mono: HW535USB (Over the Ear), HW545USB (OTE, Over the Head)**

**Section 1194.41 Information, Documentation and Support**

<i>Criteria</i>	<b>Supporting Features</b>	<i>Remarks and explanations</i>
(a) Product support documentation provided to end-users shall be made available in alternate formats upon request, at no additional charge.	<b>Supports</b>	All VPAT 13 Products listed have Product support documentation provided to end-users available in alternate formats upon request, at no additional charge.
(b) End-users shall have access to a description of the accessibility and compatibility features of products in alternate formats or alternate methods upon request, at no additional charge.	<b>Supports</b>	A description of the accessibility and compatibility features of products can be obtained upon request via email, fax, web site or telephone.
(c) Support services for products shall accommodate the communication needs of end-users with disabilities.	<b>Supports</b>	Support services for people with speech and hearing disabilities are available through TTY, email, fax and Live Chat.